



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GHC2015 Type GHC BRKR 2P 15A 277/480VAC Max 125/250VDC Max *Eaton Corp*

Catalog Number	GHC2015
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHC, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 15A, 480Y/277 Vac, 125/250 VDC, 65 Kaic At 240 Vac, 14 Kaic At 480Y/277 Vac, 50/60 HZ
Weight per unit	1.1 (lbs/each)
Product Category	2 Pole

Features

Current Rating	15 A
dimensions	2.6300 IN X 2.0000 IN X 4.8800 IN
frame	G
media	Yes
Poles	2
Voltage Rating	480Y/277 Vac, 125/250 Vdc

Descriptions

Description	TYPE GHC BRKR 2P 15A 277/480VAC MAX 125/250VDC MAX
extra long description	ETN GHC2015 GHC CB 2P 15A 277/480VA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, G-frame, GHC, Complete breaker, Fixed thermal, fixed magnetic trip type, Two-pole, 15A, 480Y/277 Vac, 125/250 Vdc, 65 kAIC at 240 Vac, 14 kAIC at 480Y/277 Vac, 50/60 Hz
Product Type	GHC CB 2P 15A 277/480VAC Max 125/250VDC

Manufacturer Information

Brand	Eaton
GTIN	00786679174074
Manufacturers Part Number	GHC2015
UPC	786679174074



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description MOLDED CASE BREAKERS

Type Molded case circuit breaker

Packaging

Carton 1

Weight Per each 1.1

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies and
EOEMs - Other

standard UL Listed