

GROUND CLAMPS
Economy and
360° Swing Type Hubs
GH, GHM SERIES



ECONOMY 360° HUB FOR GROUND CLAMPS

- Threaded hub cast of high-strength, highly conductive bronze.
- Used with ground clamp to ground conductor to water pipe.

All dimensional data is listed in inches.

CAT. NO.	CONDUIT HUB SIZE	GROUND WIRE RANGE	STD. CTN. QTY.
GH-50	1/2	10 SOL – 4 STR	50
GH-75	3/4	10 SOL – 2/0 STR	25
GH-100	1	10 SOL – 3/0 STR	15

360° SWING TYPE

- Threaded hub cast of high-strength, highly conductive bronze.
- Used with ground clamp with serrated hub to ground conductor to water pipe.
- Allows entry from any direction.
- Zinc plated steel screws.



All dimensional data is listed in inches.

CAT. NO.	CONDUIT HUB SIZE	GROUND WIRE RANGE	STD. CTN. QTY.
GHM-50	1/2	10 SOL – 2/0 STR	50
GHM-75	3/4	10 SOL – 2/0 STR	75
GHM-100	1	10 SOL – 3/0 STR	15