



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GLL10 4" Mall Ins Ground Bushing

*Crouse-Hinds*

|                  |  |
|------------------|--|
| Catalog Number   | GLL10  |
| Manufacturer     | Crouse-Hinds   |
| Description      | Grounding Bushing, 4 In Trade Size, GLL Model, Insulated, #6 to 3/0 Awg Cable Size, 6.9 In Height, 1.4 In Diameter, 110 LB/100 |
| Weight per unit  | 1.2 (lbs/each)   |
| Product Category | Rigid Conduit Fittings - Steel   |

### Features

|            |   |
|------------|---|
| connection | Threaded                                  |
| dimensions | 7.0000 IN X 1.4000 IN X 6.9000 IN         |
| Material   | Malleable Iron Body, Plastic Throat Liner |

### Dimensions and Weight

|      |      |
|------|------|
| Size | 4 in |
|------|------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 4" MALL INS GROUND BUSHING   |
| extra long description | MIDWEST GLL 10 4 GRND BUSH 105C INS  |
| Features               | Crouse-Hinds series grounding bushings are used with threaded and threadless rigid/IMC conduit to provide a means of grounding conduit through an insulated bushing. |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Eaton          |
| GTIN  | 00784564123107 |
| UPC   | 784564123107   |

### Taxonomies, Classifications, and Categories

|                      |   |
|----------------------|---|
| Category Description | Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs |
| Type                 | Grounding bushing   |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 1.2 |

### Uses, Certifications, and Standards

|                    |   |
|--------------------|---|
| Application        | Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other |
| standard           | UL, CSA   |
| Temperature Rating | 105 DEG C   |