



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GLL11 5" Ground Bushing 105 C Ins 3 to 6 Al Lug

Crouse-Hinds

Catalog Number	GLL11
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series GLL Grounding Bushing, Rigid/Imc, Aluminum Lug, #3/0-6 Awg, Malleable Iron, 105°C Temperature Rating, Threaded, 5"
Weight per unit	1.7 (lbs/each)
Product Category	Rigid Conduit Fittings - Steel

Features

connection	Threaded
dimensions	9.2000 IN X 2.8000 IN X 7.5000 IN
Material	Malleable Iron Body, Plastic Throat Liner

Dimensions and Weight

Size	5 in
------	------

Descriptions

Description	5" GROUND BUSHING 105 C INS 3 TO 6 AL LUG
extra long description	MIDWEST GLL 11 5 GRND BUSH 105C INS
Features	Crouse-Hinds series grounding bushings are used with threaded and threadless rigid/IMC conduit to provide a means of grounding conduit through an insulated bushing.
Long Description	Eaton Crouse-Hinds series GLL grounding bushing, Rigid/IMC, Aluminum lug, #3/0-6 AWG, Malleable iron, 105°C temperature rating, Threaded, 5"
Product Type	5 GRND Bush 105C Insul 3 to 6 Al Lug
Special Features	With 6 To 3/0 AWG Aluminum Lug for Copper/Aluminum Grounding Conductor, Weight 140 Lb per 100

Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564123114
Manufacturers Part Number	GLL 11
UPC	784564123114

Taxonomies, Classifications, and Categories

Category Description	Locknuts, Bushings, Re-Bushings, Re-Washers, Threaded Plugs, Knockout Plugs
Type	Grounding bushing

Packaging

Carton	1
Weight Per each	1.7



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
standard	UL, CSA
Temperature Rating	105 DEG C