



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)



## Medium Time-Delay Fuse

**GMC-5-R**

**UPC:**051712642972

**Dimensions:**

- **Height:** .788 IN
- **Length:** .25 IN
- **Width:** .197 IN

**Weight:**.004 LB

**Warranties:**

- Not Applicable

**Specifications:**

- **Type:** Electronic- small dimension
- **Application:** Electronic circuits
- **Amperage Rating:** 5A
- **Voltage Rating:** 125 Vac, 32 Vdc (self certified)
- **Interrupt Rating:** 10 kAIC at 125 Vac
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Used With:** out axial leads
- **Response Time:** 60 min maximum at 135%, 2 min maximum at 200%
- **Material:** Glass tube, nickel-plated brass endcaps
- **Connection:** Ferrule end X ferrule end

**Supporting documents:**

- [GMC 5A BUSS FUSE](#)

**Certifications:** No Data

**Product compliance:**

- CE Marked
- RoHS Compliant



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)



## Medium Time-Delay Fuse

**GMC-5-R**

**UPC:**051712642972

**Dimensions:**

- **Height:** .788 IN
- **Length:** .25 IN
- **Width:** .197 IN

**Weight:**.004 LB

**Warranties:**

- Not Applicable

**Specifications:**

- **Type:** Electronic- small dimension
- **Application:** Electronic circuits
- **Amperage Rating:** 5A
- **Voltage Rating:** 125 Vac, 32 Vdc (self certified)
- **Interrupt Rating:** 10 kAIC at 125 Vac
- **Fuse Indicator:** Non Indicating
- **Packaging Type:** Standard
- **Used With:** out axial leads
- **Response Time:** 60 min maximum at 135%, 2 min maximum at 200%
- **Material:** Glass tube, nickel-plated brass endcaps
- **Connection:** Ferrule end X ferrule end

**Supporting documents:**

- [GMC 5A BUSS FUSE](#)

**Certifications:** No Data

**Product compliance:**

- CE Marked
- RoHS Compliant