



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GMC63MA Miniature Fuse

Bussmann Fuses

Catalog Number	GMC63MA
Manufacturer	Bussmann Fuses
Description	63MA 250V 5MM X 20MM Glass, Medium Time Delay Fuse
Weight per unit	0.0020 (lbs/each)
Product Category	Tools & Testers

Features

amperage rating	63 mA
connection	Ferrule End X Ferrule End
Response Time	60 Min Maximum at 135%, 2 Min Maximum at 200%
type of indicators	Non-Indicating
Voltage Rating	250 VAC

Dimensions and Weight

Size	5.20 mm Diameter X 20.00 mm Height
------	------------------------------------

Descriptions

Description	MINIATURE FUSE
extra long description	EFSE GMC-63MA UL Medium Time Delay
Long Description	63MA 250V 5mm x 20mm Glass, Medium Time Delay Fuse
Product Type	UI Medium Time Delay 5MM Glass Fuse 63ma
Special Features	Low Breaking Capacity, Interrupt Rating 35 Amp at 250 Vac, 10000 Amp at 125 Vac, Material Glass Tube, Nickel Plated Brass Endcap

Manufacturer Information

Brand	Cooper Bussmann North America
GTIN	00051712143080
Manufacturers Part Number	GMC-63MA
UPC	051712143080

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Electronic, Medium Time Delay

Packaging

Carton	1
Package	5
Weight Per each	0.002

Uses, Certifications, and Standards

Application	Electronic Circuits
standard	UL 248-14, CSA, CE