



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GRC12 1/2" Ground Rod Clamp

Burndy LLC

Catalog Number	GRC12
Manufacturer	Burndy LLC
Description	Mechanical Ground Rod Clamp, For Cable to Rod, High Strength, 10 Awg (Sol)- 2 Awg (STR), 1/2" Drive Rod, 3/8" Stud.
Weight per unit	0.1200 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	COPPER ALLOY
----------	--------------

### Descriptions

Description	1/2" GROUND ROD CLAMP
extra long description	BUR GRC12 1/2 IN GRD ROD CLAMP
Long Description	Mechanical Ground Rod Clamp, For Cable to Rod, High Strength, 10 AWG (Sol)- 2 AWG (Str), 1/2" Drive Rod, 3/8" Stud.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Slips Over End Of Rod, One-Wrench Installation, UL467 Listed For Direct Burial In Earth And Concrete, Ground Rod Size: 1/2 IN, Stud/bolt Size: 3/8 IN, Width: 0.89 IN, Length: 0.63 IN, Height: 2 IN

### Manufacturer Information

Brand	BURNDY
GTIN	00781810230947
Manufacturers Part Number	GRC12
UPC	781810230947

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GRC, High Strength

### Packaging

Carton	1
Weight Per each	0.12

### Uses, Certifications, and Standards

Application	For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Direct Burial Applications In Earth And Concrete
standard	UL467