

Eaton GUAL26

Catalog Number: GUAL26

Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, L shape, 3/4"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover	GUAL26
	UPC
	782274465005
Product Length/Depth	Product Height
4.38 in	4.38 in
Product Width	Product Weight
2 in	3.4 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

4

7

9

Product specifications

Shape

L

Trade size

3/4"

Cover opening diameter

3"

Material

Feraloy iron alloy

Resources

Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

Specifications and datasheets

[Eaton Specification Sheet - GUAL26](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)