

Eaton GUAX14

Catalog Number: GUAX14

Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover, 2" cover opening diameter, Feraloy iron alloy, X shape, 1/2"

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Condulet GUA conduit outlet box with cover	GUAX14
	UPC 782274468600
Product Length/Depth	Product Height
4.25 in	4.25 in
Product Width	Product Weight
1.81 in	1.85 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Division 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

4

7

9

Product specifications

Shape

X

Trade size

1/2"

Cover opening diameter

2"

Material

Feraloy iron alloy

Resources

Catalogs

[Crouse-Hinds series GUA Conduit Outlet Boxes catalog page](#)

Certification reports

[Condulet GUA and GUR Explosionproof Conduit Outlet Boxes UL certification](#)

Installation instructions

[IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes](#)

Specifications and datasheets

[Eaton Specification Sheet - GUAX14](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)