



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GW235G Gang Mas Box 1/2&3/4KO 46.9cuin

*Abb Installation Products, Inc*

|                  |  |
|------------------|--|
| Catalog Number   | GW235G   |
| Manufacturer     | Abb Installation Products, Inc   |
| Description      | Masonry Box, Pre-Galvanized, Silver, 22 Cu.In Capacity, 1 Gang, Rectangular, Knockout Cable Entry, 1/2 In;3/4 In Knockout Size, 20 Knockouts, Vertical Mount, 1 Outlet, 3-3/4 In Length, 3-1/2 In Width, 3-3/4 In Height, 1.18 LB/Ea |
| Weight per unit  | 1.2 (lbs/each)   |
| Product Category | Outlet Boxes, Etc. - Steel   |

### Features

|                  |       |
|------------------|-------|
| Knockouts        | 20    |
| Material         | Steel |
| number of outlet | 1     |

### Material, Color, and Finish

|       |        |
|-------|--------|
| Color | Silver |
|-------|--------|

### Dimensions and Weight

|      |   |
|------|---|
| Size | 3-3/4 Inches Length x 3-3/4 Inches Width x 3-1/2 Inches Depth |
|------|---|

### Descriptions

|                        |                                     |
|------------------------|-------------------------------------|
| Description            | GANG MAS BOX 1/2&3/4KO 46.9CUIN     |
| extra long description | ABB GW 235 G STL GANGABLE MSNRY BOX |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | Steel City     |
| GTIN  | 00785991920956 |
| UPC   | 785991920956   |

### Taxonomies, Classifications, and Categories

|                      |                      |
|----------------------|----------------------|
| Category Description | STEEL BOXES & COVERS |
| Type                 | Masonry Boxes        |

### Packaging

|                 |      |
|-----------------|------|
| Carton          | 10   |
| Weight Per each | 1.18 |

### Uses, Certifications, and Standards

|          |          |
|----------|----------|
| standard | UL E2969 |
|----------|----------|