



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



H1499RTAT *Delisted* 4" At Non-Ic RMDL 12V LV SHLW CLNG 12V *Cooper Lighting Solutions*

Catalog Number	H1499RTAT
Manufacturer	Cooper Lighting Solutions
Description	4" Housing Non-Ic, Air-Tite Shallow Ceiling Remodel 12V Low Voltage MR16
Weight per unit	2.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	4.167 at (12V)
Ballast Type	N/A
Lamp Type	MR16
Number of Lamps	N/A
Voltage Rating	120V
Wattage	N/A

Descriptions

Description	4" AT NON-IC RMDL 12V LV SHLW CLNG 12V
extra long description	CLS H1499RTAT 4IN NON-IC REMODEL HO
Long Description	4" Housing Non-IC, Air-Tite Shallow Ceiling Remodel 12V Low Voltage MR16
Product Type	4IN Non-Ic Remodel Housing Low VLTG
Special Features	Quick Connect wiring connectors included in junction box

Manufacturer Information

Brand	HALO
GTIN	00080083584406
Manufacturers Part Number	H1499RTAT
UPC	080083584406

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	4" H1499 Low Voltage Housing

Packaging

Carton	1
Package	6
Weight Per each	2

Uses, Certifications, and Standards

Application	lighting
standard	UL/cUL Listed - Damp Location;UL/cUL Listed - Wet Location;Airtite