



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



H33GL400DX 400W ED37 Mercury Vapor White Mogul Base Lamp

Sylvania-Ledvance

Catalog Number	H33GL400DX
Manufacturer	Sylvania-Ledvance
Description	OBS69450 400W, H33, Mogul Based Mercury Lamp, Coated, Bright White Deluxe.
Weight per unit	0.8500 (lbs/each)
Product Category	Lighting

Features

average life	24000
Base	E39
lumens	7700;7700.0000
Shape	ED28
Wattage	175

Material, Color, and Finish

color rendering index (cri)	43
color temperature	5900.0000000000000000
Finish	COATED

Descriptions

Description	400W ED37 MERCURY VAPOR WHITE MOGUL BASE LAMP
extra long description	SYL H33GL-400/DX/69450 H33GL400DX 6
Long Description	OBS69450 400W, H33, mogul based Mercury lamp, coated, bright white deluxe.
Product Type	H33GL400DX 6/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135694509
Manufacturers Part Number	H33GL-400/DX/69450
UPC	046135694509

Taxonomies, Classifications, and Categories

Category Description	MERCURY VAPOR
Type	High Intensity Discharge (HID)

Packaging

Carton	1
Package	6
Weight Per each	0.85

Uses, Certifications, and Standards

standard	H33
----------	-----