



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL1392D 30A 600V 2P Disc SW W/Nema 1 Plas *Hubbell Wiring Devices*

Catalog Number	HBL1392D
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V Ac, Back and Side Wired, Black, In Nema 1 Non Metallic Enclosure
Weight per unit	1.5 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

Features

connection	Pressure Screw Terminals
Current Rating	30:30
Enclosure Type	Nema 1
Number of Phases	Single
Poles	Double Pole
Power Rating	18000
terminals	Terminal Screws
Voltage Rating	600

Dimensions and Weight

Size	4.52 in x 3.97 in x 3.43 in
------	-----------------------------

Descriptions

Construction	Fabricated
Description	30A 600V 2P DISC SW W/NEMA 1 PLAS
extra long description	HWDK HBL1392D 30A 600V 2P DISC SW W
Long Description	Switches and Lighting Controls, Industrial Grade, Toggle Switches, Motor Disconnects, Double Pole, 30A 600V AC, Back and Side Wired, Black, In NEMA 1 Non Metallic Enclosure
Product Type	30A 600V 2P Disc SW W/Nema 1 Plas
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585202631
Manufacturers Part Number	HBL1392D
series	Non-Fused
UPC	783585202631

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
----------------------	-------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 1.5

Uses, Certifications, and Standards

Application Standard Toggle

Mounting Screw Mount

standard CSA-C22.2 No.14 Industrial Control File LR-46186;UL 508,
Industrial Control File #E70402

Temperature Rating Minimum Continuous -40 Deg C without Impact