



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL14W33A Plug W/Tight 5-20P 20A 125V YI

Hubbell Wiring Devices

Catalog Number	HBL14W33A
Manufacturer	Hubbell Wiring Devices
Description	Straight Blade Devices, Thermoplastic Elastomer Water Tight, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P, Yellow, Single Pack.
Weight per unit	0.2000 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

### Features

amperage rating	20
connection	Screwed Terminal
Cord Type	All Portable
Current Rating	20
Material	Elastomeric/Composite
Number of Wires	3-Wire
pallet quantity	2025
Phase	1
Poles	2-Pole
Voltage Rating	125
Wattage	2500;2500.0000
Wire Size	#14 to #12

### Dimensions and Weight

Size	Standard Sized
------	----------------

### Descriptions

Description	PLUG W/TIGHT 5-20P 20A 125V YL
extra long description	HWDK HBL14W33A PLUG, W/TIGHT, 5-20P
Long Description	Straight Blade Devices, Thermoplastic Elastomer Water Tight, Industrial/Commercial Grade, Straight, 2-Pole 3-Wire Grounding, 20A 125V, 5-20P, Yellow, Single Pack.
Product Type	Plug, W/Tight, 5-20P, 20A 125V, YI
Special Features	Watertight

### Manufacturer Information

Brand	Hubbell Wiring Devices
GTIN	00783585131184
Manufacturers Part Number	HBL14W33A
series	Watertight Devices
UPC	783585131184



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Commercial cord connectors
Type	Plugs

## Packaging

Carton	1
Package	25
Weight Per each	0.2

## Uses, Certifications, and Standards

Application	Industrial/Commercial
environmental conditions	Watertight
Mounting	Cord
nema rating	5-20P
standard	Certified to CSA C22.2 No. 42;IP69K rating;Listed to UL498;Meets NEMA WD-1, WD-6 And ANSI Standards;UL Listed, CSA Certified to Type 4, 4X, 12, 6, 6P