



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBL2333 LKG Conn, 20A 277V Ac, L7-20R, B/W** *Hubbell Wiring Devices*

|                  |   |
|------------------|---|
| Catalog Number   | HBL2333   |
| Manufacturer     | Hubbell Wiring Devices  |
| Description      | Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 20A 277V Ac, 2-Pole 3-Wire Grounding, Nema L7-20R, Screw Terminal, Black and White Nylon. |
| Weight per unit  | 0.3500 (lbs/each)   |
| Product Category | Plugs, Connectors, Inlets, Out  |

### **Features**

|                      |                         |
|----------------------|-------------------------|
| amperage rating      | 20                      |
| connection           | Pressure Screw Terminal |
| Current Rating       | 20                      |
| insulation           | Insulated Body          |
| Material             | Nylon                   |
| Number of Conductors | 3                       |
| pallet quantity      | 2880                    |
| Poles                | 2-Pole                  |
| Voltage Rating       | 277                     |

### **Material, Color, and Finish**

|       |             |
|-------|-------------|
| Color | Black;White |
|-------|-------------|

### **Dimensions and Weight**

|      |                             |
|------|-----------------------------|
| Size | 2.26 in x 2.26 in x 3.86 in |
|------|-----------------------------|

### **Descriptions**

|                        |   |
|------------------------|---|
| Description            | LKG CONN, 20A 277V AC, L7-20R, B/W  |
| extra long description | HWDK HBL2333 LKG CONN, 20A 277V AC,   |
| Long Description       | Locking Devices, Twist-Lock®, Industrial, Female Insulgrip® Connector Body, 20A 277V AC, 2-Pole 3-Wire Grounding, NEMA L7-20R, Screw Terminal, Black and White Nylon. |
| Product Type           | LKG Conn, 20A 277V Ac, L7-20R, B/W  |
| Special Features       | Standard Product  |

### **Manufacturer Information**

|                           |                       |
|---------------------------|-----------------------|
| Brand                     | WIRING DEVICE-KELLEMS |
| GTIN                      | 00783585037929        |
| Manufacturers Part Number | HBL2333               |
| UPC                       | 783585037929          |

### **Taxonomies, Classifications, and Categories**

|                      |   |
|----------------------|---|
| Category Description | NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES |
| Type                 | Connector Body                                      |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 30   |
| Weight Per each | 0.35 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Heavy Duty Industrial   |
| environmental conditions | Indoor Dry unless protected by additional means                                     |
| Mounting                 | Cord  |
| nema rating              | L7-20R  |
| standard                 | Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498                     |
| Temperature Rating       | Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact. |