



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBL2620SW LKG WT S/SHRD RCPT, 30A 250V, L6-30R, Gy

Hubbell Wiring Devices

Catalog Number	HBL2620SW
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Watertight Safety-Shroud®, Receptacle, 30A 250V Ac, 2-Pole 3-Wire Grounding, Nema L6-30R, Screw Terminal, PBT Housing and Flange, Gray
Weight per unit	0.5500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	30
connection	Screw Terminal
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
Material	Valox™
Number of Wires	3-Wire
pallet quantity	1000
Phase	1
Poles	2-Pole
Voltage Rating	250 V
Wattage	7,500
Wire Size	#16 to #8

### Dimensions and Weight

Size	3.75 in x 3.75 in x 2.69 in
------	-----------------------------

### Descriptions

Description	LKG WT S/SHRD RCPT, 30A 250V, L6-30R,GY
extra long description	HWDK HBL2620SW LKG WT S/SHRD RCPT,
Long Description	Locking Devices, Twist-Lock®, Watertight Safety-Shroud®, Receptacle, 30A 250V AC, 2-Pole 3-Wire Grounding, NEMA L6-30R, Screw Terminal, PBT housing and flange, Gray
Product Type	LKG WT S/SHRD RCPT, 30A 250V, L6-30R, Gy
Special Features	Shrouded Watertight Construction

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585231662
Manufacturers Part Number	HBL2620SW
UPC	783585231662



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Device

## Packaging

Carton	1
Package	5
Weight Per each	0.55

## Uses, Certifications, and Standards

Application	Heavy Duty Industrial Shrouded Watertight
environmental conditions	Watertight
Mounting	Screw Mount
nema rating	I6-30R
standard	UL Listed, CSA Certified To Type 4, 4X And Type 12