



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL2740 LKG RCPT, 30A 3P 600V, L17-30R, BK *Hubbell Wiring Devices*

Catalog Number	HBL2740
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 30A 3-Phase Delta 600V Ac, 3-Pole 4-Wire Grounding, L17-30R, Screw Terminal, Black
Weight per unit	0.2500 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	30
connection	Screw Terminal
Current Rating	30
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	4-Wire
pallet quantity	2730
Phase	3
Poles	3-Pole
Voltage Rating	3 Phase 600 VAC
Wattage	18,000
Wire Size	#16 to #8

Dimensions and Weight

Size	3.28 in x 1.7 in x 1.31 in
------	----------------------------

Descriptions

Description	LKG RCPT, 30A 3P 600V, L17-30R, BK
extra long description	HWK HBL2740 LKG RCPT, 30A 3P 600V,
Long Description	Locking Devices, Twist-Lock®, Industrial, Flush Receptacle, 30A 3-Phase Delta 600V AC, 3-Pole 4-Wire Grounding, L17-30R, Screw Terminal, Black
Product Type	LKG RCPT, 30A 3P 600V, L17-30R, BK
Special Features	Standard

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585236179
Manufacturers Part Number	HBL2740
UPC	783585236179



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Single Flush Receptacle

Packaging

Carton	1
Package	10
Weight Per each	0.25

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	L17-30R
standard	Certified to CSA C22.2 No.42;Fed.Spec. W-C-596;Listed to UL 498