



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL4710 LKG SGL RCPT, 15A 125V, L5-15R, BK *Hubbell Wiring Devices*

Catalog Number	HBL4710
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, Nema L5-15R, Screw Terminal, Black.
Weight per unit	0.2000 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	15
connection	Screw Terminal
Current Rating	15
Dielectric Strength	Withstands 2,000V minimum
Material	Nylon
Number of Wires	3-Wire
Phase	1
Poles	2-Pole
Voltage Rating	125 V
Wattage	1,875
Wire Size	#18 to #10

Dimensions and Weight

Size	3.28 in x 1.53 in x 1.27 in
------	-----------------------------

Descriptions

Description	LKG SGL RCPT, 15A 125V, L5-15R, BK
extra long description	HWDK HBL4710 LKG SGL RCPT, 15A 125V
Long Description	Locking Devices, Twist-Lock®, Industrial, Single Flush Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, NEMA L5-15R, Screw Terminal, Black.
Product Type	LKG SGL RCPT, 15A 125V, L5-15R, BK
Special Features	Standard

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585236728
Manufacturers Part Number	HBL4710
UPC	783585236728



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	RECEPTACLE

Availability

Status	Inactive
--------	----------

Packaging

Carton	1
Package	10
Weight Per each	0.2

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Screw Mount
nema rating	L5-15R
standard	Certified to CSA C22.2 No.42;Fed. Spec. W-C-596;Listed to UL 498