



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HBL7484 LKG Conn, Midget, 15A 125/250V, ML-3R *Hubbell Wiring Devices*

Catalog Number	HBL7484
Manufacturer	Hubbell Wiring Devices
Description	Locking Devices, Midget Twist-Lock®, Industrial, Female Straight Connector, 15A 125/250V Ac, 3-Pole 3-Wire Non Grounding, Nema ML-3R, Screw Terminal, Black.
Weight per unit	0.0500 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
connection	Pressure Screw Terminal
Current Rating	15
insulation	Insulated Body
Material	Nylon
Number of Conductors	3
pallet quantity	6600
Poles	3-Pole
Voltage Rating	125/250 V

Material, Color, and Finish

Color	Black
-------	-------

Dimensions and Weight

Size	1.17 in x 1.17 in x 2.42 in
------	-----------------------------

Descriptions

Description	LKG CONN, MIDGET, 15A 125/250V, ML-3R
extra long description	HWDK HBL7484 LKG CONN, MIDGET, 15A
Long Description	Locking Devices, Midget Twist-Lock®, Industrial, Female Straight Connector, 15A 125/250V AC, 3-Pole 3-Wire Non Grounding, NEMA ML-3R, Screw Terminal, Black.
Product Type	LKG Conn, Midget, 15A 125/250V, ML-3R
Special Features	Standard Product

Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585237381
Manufacturers Part Number	HBL7484
UPC	783585237381

Taxonomies, Classifications, and Categories

Category Description	NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES
Type	Connector Body



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	10
Weight Per each	0.05

Uses, Certifications, and Standards

Application	Heavy Duty Industrial
environmental conditions	Indoor Dry unless protected by additional means
Mounting	Cord
nema rating	ML-3R
standard	Certified to CSA C22.2 No.42;Listed to UL 498
Temperature Rating	Maximum Continuous: 75° C; Minimum Continuous: -40° C w/o impact, -25° with impact.