



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## HBLDS6 Disconnect, 60A Unfused, 4X *Hubbell Wiring Devices*

Catalog Number	HBLDS6
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, 60A 600V Ac, Screw Terminals, Gray, Nema 4X Enclosure
Weight per unit	5.5 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

### Features

action	Snap
amperage rating	60
connection	Terminal Screws
Contact Configuration	Two Position
Contact Rating	60A
Current Rating	60
Material	COMPOSITE
operating cycles	6,000
pallet quantity	140
Poles	3
Switch Type	Lever
Voltage Rating	600
Wattage	36000;36000.0000

### Dimensions and Weight

Size	11 in x 7.75 in x 5.94 in
------	---------------------------

### Descriptions

Description	DISCONNECT, 60A UNFUSED, 4X
extra long description	HWDK HBLDS6 DISCONNECT, 60A UNFUSED
Features	NEC section 430.102(B) requires each motor controller to have a disconnect within line of sight from the motor and driven equipment. Hubbell's Circuit-Lock® Unfused Disconnect Switches are UL listed as a manual motor controller and also "suitable as a motor disconnect" and meet these code requirements.
Long Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Unfused Switch, 60A 600V AC, Screw Terminals, Gray, NEMA 4X Enclosure
Product Type	Disconnect, 60A Unfused, 4X
Special Features	Standard Product



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585430706
Manufacturers Part Number	HBLDS6
series	Non-Fused
UPC	783585430706

## Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	Disconnect Switches

## Availability

Status	Inactive
--------	----------

## Packaging

Carton	1
Weight Per each	5.5

## Uses, Certifications, and Standards

Application	Labelless
Enclosure	Type 4X, IP69k
environmental conditions	NEMA 4X
Mounting	Mounting Feet
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
standard	UL Listed