



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **HBLDS60100RS Rep Disco Switch, 60A,** *Hubbell Wiring Devices*

Catalog Number	HBLDS60100RS
Manufacturer	Hubbell Wiring Devices
Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Replacement Switch, Three Pole, 60A 600V Ac, Screw Terminals, Gray
Weight per unit	0.4530 (lbs/each)
Product Category	Non-Fusible Disconnect Safety

### **Features**

amperage rating	60/100
connection	Terminal Screws
Contact Configuration	Two Position
Contact Rating	100A
Material	COMPOSITE
Poles	3

### **Dimensions and Weight**

Size	Standard Sized
------	----------------

### **Descriptions**

Description	REP DISCO SWITCH, 60A,
extra long description	HWDK HBLDS60100RS REP DISCO SWITCH,
Features	NEC section 430.102(B) requires each motor controller to have a disconnect within line of sight from the motor and driven equipment. Hubbell's Circuit-Lock® Unfused Disconnect Switches are UL listed as a manual motor controller and also "suitable as a motor disconnect" and meet these code requirements.
Long Description	Switches and Lighting Controls, Industrial Grade, Disconnect Switches, Replacement Switch, Three Pole, 60A 600V AC, Screw Terminals, Gray
Product Type	Rep Disco Switch, 60A,
Special Features	Standard Product

### **Manufacturer Information**

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585955216
Manufacturers Part Number	HBLDS60100RS
series	Fused;Non-Fused
UPC	783585955216



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description DISCONNECTS

Type Accessories

## Packaging

Carton 1

Package 10

Weight Per each 0.453

## Uses, Certifications, and Standards

Application For 60 and 100A HBLDS6 Series

environmental conditions Indoor Dry unless protected by additional means

standard UL Listed