



MILBANK
ENERGY AT WORK



HC664JIC12

| | |
|-------------------------------|---|
| Catalog Number | HC664JIC12 |
| Marketing Product Description | 6x4X6 Hinge Cover Type 12 UL Listed Steel No Knockouts ANSI 61 Gray Continuous Hinge Clamps And Screws Gasket In Door Mounting Feet Welded Seams |
| UPC | 784572112681 |
| Length (IN) | 4 |
| Width (IN) | 6 |
| Height (IN) | 6 |
| Weight (LB) | 4 |
| Brand Name | Milbank |
| Type | Hinge Cover |
| Application | Enclosure for Mounting Electrical Equipment |
| Standard | UL Listed |
| Number Of Outlet | 0 |
| Material | Steel with Powder Coat Finish |
| Size | 4L x 6W x 6H |
| Color | ANSI 61 Gray |
| Construction | Welded |
| Cable Entry | No Knockouts |
| Mounting | Wall Mount |
| NEMA Rating | Type 12 |

| | |
|------------|--|
| Hinge Type | Continuous Hinge with Removable Pin |
| Top | Plain Top |
| Door | 1 Gasketed Door |
| Latch | Clamp and Screw on One Side |
| Support | Panel Supports |

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.



MILBANK
ENERGY AT WORK



HC664JIC12

| | |
|-------------------------------|---|
| Catalog Number | HC664JIC12 |
| Marketing Product Description | 6x4X6 Hinge Cover Type 12 UL Listed Steel No Knockouts ANSI 61 Gray Continuous Hinge Clamps And Screws Gasket In Door Mounting Feet Welded Seams |
| UPC | 784572112681 |
| Length (IN) | 4 |
| Width (IN) | 6 |
| Height (IN) | 6 |
| Weight (LB) | 4 |
| Brand Name | Milbank |
| Type | Hinge Cover |
| Application | Enclosure for Mounting Electrical Equipment |
| Standard | UL Listed |
| Number Of Outlet | 0 |
| Material | Steel with Powder Coat Finish |
| Size | 4L x 6W x 6H |
| Color | ANSI 61 Gray |
| Construction | Welded |
| Cable Entry | No Knockouts |
| Mounting | Wall Mount |
| NEMA Rating | Type 12 |

| | |
|------------|--|
| Hinge Type | Continuous Hinge with Removable Pin |
| Top | Plain Top |
| Door | 1 Gasketed Door |
| Latch | Clamp and Screw on One Side |
| Support | Panel Supports |

Please consult serving utility for their requirements prior to ordering or installing, as specifications and approvals vary by utility and may require local electrical inspector approval. All installations must be installed by a licensed electrician and must comply with all national and local codes, laws and regulations. Milbank reserves the right to make changes in specifications and features shown without notice or obligation.