

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1701 North Jackson Suite E 78501-0000, TX McAllen Phone: 956-331-2410 Fax: 956-331-2411



Weight Per each

HEBAA 30A 600V 13/32" X 1-1/2" Midget Inline Fuse Holder *Bussmann Fuses*

| Catalog Number | HEBAA |
|-----------------------------------|--|
| Manufacturer | Bussmann Fuses |
| Description | Eaton Bussmann Series Heb Inline Fuse Holder, 30 A, Single-Pole, Loadside: Copper Crimp #8-16; (2) #12-16, Lineside: Copper Crimp #8-16; (2) #12-16, 200 Kaic, 600 V |
| Weight per unit | 0.0800 (lbs/each) |
| Product Category | Fuseholders & Fuseblks |
| eatures | |
| amperage rating | 30 |
| connection | (2) #12-16;(2) #12-16Loadside: Copper crimp #8-16;Lineside: Copper crimp #8-16 |
| dimensions | 0.0010 IN X 0.0010 IN X 0.0010 IN |
| media | Yes |
| Voltage Rating | 600 V |
| escriptions | |
| - Description | 30A 600V 13/32" X 1-1/2" MIDGET INLINE FUSE HOLDER |
| extra long description | EFSE HEB-AA BUSS FUSEHOLDER |
| Features | Supplemental fuse holders, clips and blocks to meet any type of application that may be out there |
| Long Description | Eaton Bussmann series HEB inline fuse holder, 30 A, Single-pole, Loadside: Copper crimp #8-16; (2) #12-16, Lineside: Copper crimp #8-16; (2) #12-16, 200 kAIC, 600 V |
| Product Type | Buss Fuseholder |
| Special Features | 1 Pole, Waterproof, Non Breakaway, For Use With 13/32 In X 1-1/2 In BAF, FNM, FNQ, KTK Fuse |
| Nanufacturer Information | |
| Brand | Eaton Bussmann series |
| GTIN | 00051712718202 |
| Manufacturers Part Number | HEB-AA |
| UPC | 051712718202 |
| axonomies, Classifications, and (| Categories |
| Category Description | LISE BLOCKS FUSE HOLDEDS |
| Туре | Inline fuse holder |
| ackaging | |
| Carton | 10 |
| | |

0.08

1701 North Jackson Suite E 78501-0000, TX McAllen Phone: 956-331-2410 Fax: 956-331-2411

Uses, Certifications, and Standards

| Application | Stationary Mach Equip In Factory - Robotics |
|-------------|--|
| standard | Contact Manufacturer, CSA Certified, UL Recognized, RoHS |
| | Compliant |