



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

805 South Timberlane Drive
71730-0000, AR El Dorado
Phone: 870-639-6289
Fax: 870-864-8850



HJ1614HWPL2LG 15.8X13.8X6 N4X FG FLT HC

Hoffman Enclosures, Inc.

Catalog Number	HJ1614HWPL2LG
Manufacturer	Hoffman Enclosures, Inc.
Description	Flat Cover With Latches Type 4X, 15.81X13.81X5.99, LT Gray, Fiberglass
Weight per unit	10.0 (lbs/each)
Product Category	Nema Types 4, 4X, 12 & 13

Features

ip rating	IP66
Material	Fiberglass

Material, Color, and Finish

Color	Light Gray
Color Code	RAL 7035
Finish	Smooth Matte
Style	No Window

Dimensions and Weight

Depth	5.99
Height	15.81
Size	17.31x15.30x6.70 in
Width	13.81

Descriptions

Description	15.8X13.8X6 N4X FG FLT HC
extra long description	NVENT HOF HJ1614HWPL2LG TYPE 4X, FL
Features	Enclosures feature a flat, overlapping cover design that ensures a more-secure seal. Available with solid and window covers. Latches provide easy access and security.
Long Description	Flat Cover with Latches Type 4X, 15.81x13.81x5.99, Lt Gray, Fiberglass
Product Type	Type 4X, Flat HNG Latch CVR
Short Description	TYPE 4X, FLAT HNG LATCH CVR

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510158910
Manufacturers Part Number	HJ1614HWPL2LG
UPC	783510158910

Taxonomies, Classifications, and Categories

Category Description	VYNCKIER FIBERGLASS ENCLOSURES
Type	Fiberglass and Thermoplastic Wall Mounted Industrial Enclosures



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

805 South Timberlane Drive
71730-0000, AR El Dorado
Phone: 870-639-6289
Fax: 870-864-8850

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 10

Uses, Certifications, and Standards

Application Corrosive Environments, Controls and Drives

nema rating 4X Watertight, corrosion-resistant