



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLBC6LS9FSD2WE0 6" Led Slim DWNLT CCT Canless or Retrofit 120/277V *Cooper Lighting Solutions*

Catalog Number	HLBC6LS9FSD2WE0
Manufacturer	Cooper Lighting Solutions
Description	6" Downlight, 900/1100 Selectable Lumens, 90 Cri Selectable CCT D2W Option 120/277V 60HZ, 0-10V Dimmable Matte White Flange Canless or Retrofit Installation Compliant All States But Ca
Weight per unit	2.0 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.059A at 277V
Lamp Type	LED
Voltage Rating	120/277V
Wattage	16.5 W

Material, Color, and Finish

Finish	Matte White
Style	(blank)

Descriptions

extra long description	CLS HLBC6LS9FSD2WE010MWR 6" HLB COM
Long Description	6" downlight, 900/1100 selectable lumens, 90 CRI selectable CCT D2W option 120/277V 60Hz, 0-10V dimmable matte white flange canless or retrofit installation compliant all states but CA
Product Type	6" HLB Comfort, LS, 5CCT, D2W, R, Unv
Special Features	Available in 4" and 6"

Manufacturer Information

Brand	HALO
GTIN	00080083263257
Manufacturers Part Number	HLBC6LS9FSD2WE010MWR
UPC	080083263257

Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	HLBC Slim Regressed Canless Downlight

Packaging

Carton	1
Weight Per each	2.03



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	CEILING
standard	Energy Star Certified; IECC Compliant; Title 20 Compliant; Title 24 Compliant; UL Listed; RoHS Compliant