



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



HLS4079501EWH6BP 4" 12W Led Disk Light 50K 90CRI 120V 750LM 6 Pack

Cooper Lighting Solutions

Catalog Number	HLS4079501EWH6BP
Manufacturer	Cooper Lighting Solutions
Description	4" Led Surface Light, 700 Lumens (Nominal), 90 Cri Minimum, 5000K CCT, 120V 60HZ, Le and Te Phase, Matte White Flange Cut 10 Percent Dimming, Qty 6 Bulk Pack (Not For Individual Sale)
Weight per unit	3.1 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.103A
Lamp Type	LED
Voltage Rating	120V
Wattage	12.4 W

Material, Color, and Finish

Finish	Matte White
Style	(blank)

Descriptions

Description	4" 12W LED DISK LIGHT 50K 90CRI 120V 750LM 6 PACK
extra long description	CLS HLS4079501EWH-6BP HLS, 4IN, 750
Long Description	4" LED surface light, 700 lumens (nominal), 90 CRI minimum, 5000K CCT, 120V 60Hz, LE and TE phase, matte white flange cut 10 percent dimming, Qty 6 bulk pack (not for individual sale)
Product Type	HLS, 4IN, 750LM, 5000K, Wet, 6PK
Special Features	Sizes include 4", 6", & 9"

Manufacturer Information

Brand	HALO
GTIN	00080083256709
Manufacturers Part Number	HLS4079501EWH-6BP
UPC	080083256709

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	HLS Round LED Surface Mount

Packaging

Carton	1
Weight Per each	3.06



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	Surface Mount
standard	Energy Star; IECC Compliant; UL Listed; Title 24 Compliant; RoHS Compliant