



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IOP2P32N35I 2LT 277V Flu Bal

Advance By Signify

| | |
|------------------|---|
| Catalog Number | IOP2P32N35I |
| Manufacturer | Advance By Signify |
| Description | The Right Choice For A Broad Range Of New Construction and Retrofit Applications Compatible With Energy Saving Lamps;Eligible For Utility Rebates;Maximizes Fixture Design;Reduces Packaging Waste Reliable and Energy Efficient Philips Advance'S Centium Commercial Grade Specifications, Plus Added Benefits Of Lamp Striation Reduction Technology. Intellivolt (120-277V) Input Voltage Range;Lamp Striation Reduction;Meets Nema Premium/Cee;Smallest Enclosure In Industry General Office Lighting, Institutional, Gover |
| Weight per unit | 0.8000 (lbs/each) |
| Product Category | Electronic Linear Fluorescent |

Features

| | |
|---------------------------|---------------|
| Ballast Factor | 0.88 |
| Lamp Type | T8 |
| Number of Lamps | 2 |
| Power Factor | 0.98 |
| start type | Instant Start |
| total harmonic distortion | 10 |
| Voltage Rating | 120-277 |
| Wattage | 32 |
| Wire Type | SOLID |

Material, Color, and Finish

| | |
|------------------|-------|
| Housing Material | Metal |
|------------------|-------|

Dimensions and Weight

| | |
|--------|------|
| Height | 3.94 |
| Width | 5.12 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 2LT 277V FLU BAL |
| extra long description | ADV 498634 ELE BALLAST (2) F32T8 12 |
| Long Description | The right choice for a broad range of new construction and retrofit applications Compatible with Energy Saving lamps;Eligible for Utility Rebates;Maximizes fixture design;Reduces packaging waste Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology. IntelliVolt (120-277V) input voltage range;Lamp Striation Reduction;Meets NEMA Premium/CEE;Smallest enclosure in industry General office lighting, institutional, gover |
| Product Type | Ele Ballast (2) F32T8 120-277V |
| Special Features | UL, CSA, NEMA Premium, RoHS |

Manufacturer Information

| | |
|---------------------------|---------------------|
| Brand | Signify Electronics |
| GTIN | 00781087125076 |
| Manufacturers Part Number | 498634 |
| UPC | 781087125076 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------|
| Category Description | ELECTRONIC BALLAST |
| Type | Electronic Fluorescent |

Packaging

| | |
|-----------------|-----|
| Carton | 1 |
| Weight Per each | 0.8 |

Uses, Certifications, and Standards

| | |
|------------------|--|
| Frequency Rating | 50to60 |
| standard | CSA certificate;UL certificate;CEC Listing;CEE Rated;CSA E;NEMA Premium;RoHS Compliant |