



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC1P 4IN Ic HSG

Lithonia Lighting - Acuity

Catalog Number	IC1P
Manufacturer	Lithonia Lighting - Acuity
Description	The Energy-Efficient, Air-Loc Sealed Double Wall Construction Housing Stops Infiltration and Exfiltration Of Air, Reducing Heating and Cooling Costs Without An Extra Gasket. The 4-Inch Ic Housing Is Optimized For PAR20 Gimbal and Higher Wattage 120-Volt MR16 Lamps and Can Be Completely Covered With Insulation.
Weight per unit	3.5 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Lamp Type	Incandescent
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Shape	Round

Dimensions and Weight

Height	8
Length	15
Width	15

Descriptions

Construction	New Construction
Description	4IN IC HSG
extra long description	LITH IC1P 4IN Incandescent New Cons
Long Description	The energy-efficient, Air-Loc sealed double wall construction housing stops infiltration and exfiltration of air, reducing heating and cooling costs without an extra gasket. The 4-inch IC housing is optimized for PAR20 gimbal and higher wattage 120-volt MR16 lamps and can be completely covered with insulation.
Product Type	Housing

Manufacturer Information

Brand	JUNO
GTIN	00661209077196
Manufacturers Part Number	IC1P
UPC	661209077196

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
----------------------	---------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

aperture size 4 in

Packaging

Carton 1

Package 4

Weight 5

Weight Per each 3.5

Uses, Certifications, and Standards

Application Residential

environmental conditions Indoor

Mounting Recessed

standard UL