



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC22R 6" Ic Rated Remodel Reces *Lithonia Lighting*

Catalog Number	IC22R
Manufacturer	Lithonia Lighting
Description	These Ic-Rated 6-Inch Incandescent Housings Feature An Air-Loc Seal to Stop Infiltration and Exfiltration Of Air, Reducing Heating and Cooling Costs.
Weight per unit	2.0 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
media	Yes
Number of Lamps	1
Shape	Round

Dimensions and Weight

Height	7.125
Length	13.75
Width	7.125

Descriptions

Construction	Remodel
extra long description	LITH IC22R 6IN Incandescent Remodel
Features	Contractor Select
Long Description	These IC-rated 6-inch incandescent housings feature an Air-Loc seal to stop infiltration and exfiltration of air, reducing heating and cooling costs.
Product Type	Housing

Manufacturer Information

Brand	JUNO
GTIN	00661209017673
Manufacturers Part Number	IC22R
UPC	661209017673

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	Housing

Trade Size

aperture size	6 in
---------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	6
Weight	2
Weight Per each	1.96

Uses, Certifications, and Standards

Application	Residential
environmental conditions	Indoor
Mounting	Recessed
standard	cUL,UL