



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IC23W 6" RCS DBL Wall Housing, No Bracket *Lithonia Lighting*

Catalog Number	IC23W
Manufacturer	Lithonia Lighting
Description	Incandescent Airtight Housing, Round, 90 W, 120 V, Galvanized, Steel Fixture Material, Aluminum Housing Material, Non Dimmable, 6 In Aperture Size, 19 LB
Weight per unit	19.0 (lbs/each)
Product Category	Incandescent Recessed Architec

### Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
media	Yes
Number of Lamps	1
Shape	Round

### Dimensions and Weight

Height	7.75
Length	13.5
Width	17.5

### Descriptions

Construction	New Construction
Description	6" RCS DBL WALL HOUSING, NO BRACKET
extra long description	LITH IC23 W 6IN Incandescent No Pla

### Manufacturer Information

Brand	JUNO
GTIN	00661209068613
Manufacturers Part Number	IC23 W
UPC	661209068613

### Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
Type	Housing

### Packaging

Carton	1
Package	6
Weight Per each	19

### Uses, Certifications, and Standards

environmental conditions	Indoor
Mounting	Recessed
standard	CSA,UL