



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IC44N IC44N 50W MR16 Lovtg HSG W/TFMR

*Lithonia Lighting - Acuity*

Catalog Number	IC44N
Manufacturer	Lithonia Lighting - Acuity
Description	The Energy-Efficient, Air-Loc Sealed Double Wall Construction Housing Does Not Require A Separate Air-Loc Gasket to Stop Infiltration and Exfiltration Of Air and Reduce Heating and Cooling Costs
Weight per unit	31.0 (lbs/each)
Product Category	Halogen & Quartz Recessed Arch

### Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	Round

### Dimensions and Weight

Height	7.625
Length	16
Width	14

### Descriptions

Construction	New Construction
Description	IC44N 50W MR16 LOVTG HSG W/TFMR
extra long description	LITH IC44N 4IN Low Voltage New Cons
Long Description	The energy-efficient, Air-Loc sealed double wall construction housing does not require a separate Air-Loc gasket to stop infiltration and exfiltration of air and reduce heating and cooling costs
Product Type	Housing

### Manufacturer Information

Brand	JUNO
GTIN	00661209017147
Manufacturers Part Number	IC44N
UPC	661209017147

### Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
----------------------	---------------------------

### Trade Size

aperture size	4 in
---------------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	4
Weight	6
Weight Per each	31

## Uses, Certifications, and Standards

Application	Residential
environmental conditions	Indoor
Mounting	Recessed
standard	CSA,cUL