



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC926W Slope Ic HSG Qkwire *Lithonia Lighting - Acuity*

Catalog Number	IC926W
Manufacturer	Lithonia Lighting - Acuity
Description	The Double Wall New Construction Housing For Use In 2/12 to 6/12 Pitch Slopes, 9 to 27 Degrees, Can Be Completely Covered With Insulation.
Weight per unit	4.8 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Hardware	Yes
Lamp Type	Incandescent
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	OVAL
Voltage Rating	120

Material, Color, and Finish

Color	Unfinished
-------	------------

Dimensions and Weight

Height	9
Length	14
Width	14

Descriptions

Construction	New Construction
Description	SLOPE IC HSG QKWIRE
extra long description	LITH IC926 W 6IN Incandescent Slope
Long Description	The double wall new construction housing for use in 2/12 to 6/12 pitch slopes, 9 to 27 degrees, can be completely covered with insulation.
Product Type	Housing

Manufacturer Information

Brand	Juno Lighting Group
GTIN	00661209107800
Manufacturers Part Number	IC926 W
UPC	661209107800

Trade Size

aperture size	6 in
---------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	4
Weight	4
Weight Per each	4.75

Uses, Certifications, and Standards

Application	Education, Government, Healthcare, Hospitality, House of Worship, Offices & Banks, Residential, Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSA, UL