



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IC928 IC928 HSNG Sloped Ceiling Ic

Lithonia Lighting - Acuity

Catalog Number	IC928
Manufacturer	Lithonia Lighting - Acuity
Description	IC928 Downlight Is An Ic-Rated, Double Wall Construction Housing For Use In 7/12- to 12/12-Pitch Slopes, 30- to 45-Degrees, Can Be Completely Covered With Insulation.
Weight per unit	18.0 (lbs/each)
Product Category	Incandescent Recessed Architec

Features

Hardware	Yes
Lamp Type	Incandescent
Material	Aluminum
Maximum Operating Temperature	25
Number of Lamps	1
Power Source	Hardwired
Shape	OVAL
Voltage Rating	120

Material, Color, and Finish

Color	Unfinished
-------	------------

Dimensions and Weight

Height	7.625
Length	14
Width	16

Descriptions

Construction	New Construction
Description	IC928 HSNG SLOPED CEILING IC
extra long description	LITH IC928 6IN Incandescent Super S
Long Description	IC928 downlight is an IC-rated, double wall construction housing for use in 7/12- to 12/12-pitch slopes, 30- to 45-degrees, can be completely covered with insulation.
Product Type	Housing

Manufacturer Information

Brand	JUNO
GTIN	00661209000965
Manufacturers Part Number	IC928
UPC	661209000965

Taxonomies, Classifications, and Categories

Category Description	All Recessed Cans & Trims
----------------------	---------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Trade Size

aperture size 6 in

Packaging

Carton 1

Package 4

Weight 4

Weight Per each 18

Uses, Certifications, and Standards

Application Education, Government, Healthcare, Hospitality, House of
Worship, Offices & Banks, Residential, Retail

environmental conditions Indoor

Mounting Recessed

standard CSA, UL