



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ICTC113 Step Light (Needs 840WH)

Lithonia Lighting - Acuity

Catalog Number	ICTC113
Manufacturer	Lithonia Lighting - Acuity
Description	The Ic-Rated Step Light/Night Light Housing For Incandescent Lamps Is Designed For Use Indoors In Insulated and Non-Insulated Areas.
Weight per unit	1.3 (lbs/each)
Product Category	Step Lights

Features

Lamp Type	Incandescent
Maximum Operating Temperature	25
Shape	Rectangular

Dimensions and Weight

Height	5
Length	14
Width	8

Descriptions

Construction	New Construction
Description	STEP LIGHT (NEEDS 840WH)
extra long description	LITH ICTC113 Incandescent Step Light
Long Description	The IC-rated step light/night light housing for incandescent lamps is designed for use indoors in insulated and non-insulated areas.
Product Type	Step Light

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00661209102027
Manufacturers Part Number	ICTC113
UPC	661209102027

Packaging

Carton	1
Weight	0.856
Weight Per each	1.343



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Education, Government, Healthcare, Hospitality, House of Worship, Offices & Banks, Residential, Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSA, UL