



15 AMP NEMA L515 DUPLEX RECEPTACLE, ORANGE, ISOLATED GROUND

IG4700 | [Pass & Seymour](#)

FEATURES & BENEFITS

Turnlok Duplex Receptacle 3wire 15amp 125volt Isolated Ground



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate backwire capability. Accepts #14-#10 AWG.

SPECIFICATIONS

GENERAL INFO

Color: Orange

Type: Duplex, Receptacles

Number Of Wires: 3

Special Features: Isolated Ground

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121403

DIMENSIONS

Depth (US): 1.199"

Height (US): 3.281"

Width (US): 1.50"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: L515

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant





15 AMP NEMA L515 DUPLEX RECEPTACLE, ORANGE, ISOLATED GROUND

IG4700 | [Pass & Seymour](#)

FEATURES & BENEFITS

Turnlok Duplex Receptacle 3wire 15amp 125volt Isolated Ground



- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- IG symbol and Isolated Ground markings for easy identification and circuit delineation.
- One-piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate backwire capability. Accepts #14-#10 AWG.

SPECIFICATIONS

GENERAL INFO

Color: Orange

Type: Duplex, Receptacles

Number Of Wires: 3

Special Features: Isolated Ground

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Standard: Yes

UL Listing No: 498

UL Standard: Yes

UN SPSC: 39121403

DIMENSIONS

Depth (US): 1.199"

Height (US): 3.281"

Width (US): 1.50"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: L515

Volts: 125V

Volts (AC): 125

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

