

**IEC Pin and Sleeve  
Watertight Devices  
Plug/Inlet Replacement Interior**

# HUBBELL

## Features

- Thermoset Polyester Contact Carrier

## Ordering Information

<b>Description</b> Pin and Sleeve Replacement Interior, For 3W 20A, IEC	<b>UPC</b> 783585420011	<b>Catalog Number</b> <b>IN320AM</b>
-------------------------------------------------------------------------------	----------------------------	-----------------------------------------

**Device Color**  
Black



## Standards

UL Listed  
CSA Certified

## Specifications

Gaskets	Neoprene
Retainer	High-Impact Thermoset
Terminal Screws	Stainless Steel

## Performance

### Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 3,000V AC  
Max Working Voltage 600V AC RMS

### Mechanical

Impact Resistance In accordance with UL746C  
Product Identification Identification and ratings are a part of the external label and molded into the receptacle mount  
Terminal Identification Terminals identified in accordance with North American and International conventions

### Environmental

Flammability UL94-5VA and V-0 classification  
Ingress Protection IP67 Suitability  
Operating Temperatures Max. Continuous:75°C; Min. Continuous:-40°C w/o impact

## Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.



**IEC Pin and Sleeve  
Watertight Devices  
Plug/Inlet Replacement Interior**

# HUBBELL

## Features

- Thermoset Polyester Contact Carrier

## Ordering Information

<b>Description</b> Pin and Sleeve Replacement Interior, For 3W 20A, IEC	<b>UPC</b> 783585420011	<b>Catalog Number</b> <b>IN320AM</b>
-------------------------------------------------------------------------------	----------------------------	-----------------------------------------

**Device Color**  
Black



## Standards

UL Listed  
CSA Certified

## Specifications

Gaskets	Neoprene
Retainer	High-Impact Thermoset
Terminal Screws	Stainless Steel

## Performance

### Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 3,000V AC  
Max Working Voltage 600V AC RMS

### Mechanical

Impact Resistance In accordance with UL746C  
Product Identification Identification and ratings are a part of the external label and molded into the receptacle mount  
Terminal Identification Terminals identified in accordance with North American and International conventions

### Environmental

Flammability UL94-5VA and V-0 classification  
Ingress Protection IP67 Suitability  
Operating Temperatures Max. Continuous:75°C; Min. Continuous:-40°C w/o impact

## Online Resources

eCatalog

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484

Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

