



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IPLD2506 250MCM-#6 6 Pole Polaris Connector Block

Nsi Industries

Catalog Number	IPLD2506
Manufacturer	Nsi Industries
Description	Multi-Tap Connector, #6 Awg Conductor Size, 250 MCM Conductor Size, Insulated, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, 6 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 5.52 In Overall Length, 600 V, 0.7 LB/Ea
Weight per unit	0.7000 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	250 MCM-6 AWG
Wire Type	Class B & C

Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

Dimensions and Weight

Size	L=5.520 - W=2.280 - H=2.180
------	-----------------------------

Descriptions

Description	250MCM-#6 6 POLE POLARIS CONNECTOR BLOCK
extra long description	NSI IPLD250-6 5-Prt Clr MultiTp Pre
Features	The Polaris IPLD250-6 6-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to six conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 250 MCM - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric stren

Manufacturer Information

Brand	Polaris
GTIN	00662381923042
UPC	662381923042



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description SPLIT BOLTS

Type Double Sided Entry

Packaging

Carton 4

Weight Per each 0.7

Uses, Certifications, and Standards

Application Wire Termination

environmental conditions 90 C

standard UL 486A/B

Temperature Rating 90 C