



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IPLD3503 350MCM-#6 3 Pole Polaris Connector Block

*Nsi Industries*

Catalog Number	IPLD3503
Manufacturer	Nsi Industries
Description	Multi-Tap Connector, #6 Awg Conductor Size, 350 MCM Conductor Size, Insulated, Plastisol Insulation Material, Copper/Aluminum Conductor Material, Black Insulation Color, 3 Conductors, -45 °C Operating Temperature, +90 °C Operating Temperature, 3.52 In Overall Length, 600 V, 0.59 LB/Ea
Weight per unit	0.5900 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	350 MCM-6 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=3.520 - W=2.410 - H=2.610
------	-----------------------------

### Descriptions

Description	350MCM-#6 3 POLE POLARIS CONNECTOR BLOCK
extra long description	NSI IPLD350-3 POLARIS Ins Multi-Tap
Features	The Polaris IPLD350-3 3-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to three conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 350 MCM - 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric str

### Manufacturer Information

GTIN	00662381924018
UPC	662381924018



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... SPLIT BOLTS

Type ..... Double Sided Entry

## Packaging

Carton ..... 4

Weight Per each ..... 0.59

## Uses, Certifications, and Standards

Application ..... Wire Termination

environmental conditions ..... 90 C

standard ..... UL 486A/B

Temperature Rating ..... 90 C