



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## IPLD7508 750MCM 8 Tap

*Nsi Industries*

Catalog Number	IPLD7508
Manufacturer	Nsi Industries
Description	The Polaris IPLD750-8 Multi-Tap Dual-Sided Entry Connector Features 8 Ports Sized For 750 - 250 MCM Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Dual-Sided Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Installation In Cable Trays,
Weight per unit	3.7 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	Aluminum
Number of Conductors	8
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	750-250 MCM
Wire Type	Class B & C

### Material, Color, and Finish

Color	Black
Finish	Plastisol Insulated

### Dimensions and Weight

Size	L=12.080 - W=3.410 - H=3.420
------	------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	750MCM 8 TAP
extra long description	NSI IPLD750-8 POLARIS Ins Multi-Tap
Features	The Polaris IPLD750-8 8-Port Dual-Sided Connector provides the simplest solution for forming a secure connection between up to eight conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 750 - 250 MCM wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrapped in high-dielectric stren
Long Description	The Polaris IPLD750-8 Multi-Tap Dual-Sided Entry Connector features 8 ports sized for 750 - 250 MCM wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each dual-sided port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including installation in cable trays,
Product Type	Polaris Ins Multi-Tap 750 8 Port Dse
Special Features	(8) 750-250 MCM - Dual Rated

## Manufacturer Information

Brand	NSi
GTIN	00662381926067
Manufacturers Part Number	IPLD750-8
UPC	662381926067

## Taxonomies, Classifications, and Categories

Type	Double Sided Entry
------	--------------------

## Packaging

Carton	1
Weight Per each	3.73

## Uses, Certifications, and Standards

Application	Wire Termination
environmental conditions	90 C
standard	UL 486A/B
Temperature Rating	90 C