



PART NUMBER	# OF PORTS	LENGTH
ISPB350-3	3	3.61
ISPB350-4	4	4.80
ISPB350-6	6	7.18



ROCKET


THREAD CAP

5/16 INTERNAL HEX PRESSURE SCREWS


350KCMIL - #12 AWG CONDUCTOR PORT

REF. LENGTH

CUT FOR APPROPRIATE WIRE SIZE



DETAIL VIEW OF ROCKET
1:1 SCALE



CONTACT NSI FOR SALES @ 800.321.5847

NOTES:

- CONNECTOR PRE-FILLED W/ OXIDE INHIBITOR.
- CONNECTOR MEETS OR EXCEEDS ANSI C119.4 SPECIFICATIONS.



POLARIS
SALES . CO . INC

PROPRIETARY AND CONFIDENTIAL

11625 PROSPEROUS DRIVE ODESSA, FL 33556

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POLARIS SALES CO. INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POLARIS SALES CO. INC. IS PROHIBITED.

TITLE:
**350 BLACK
SUBMERSIBLE
PEDESTAL CONNECTOR**

NAME DATE
DRAWN BY S.PARRY 2/7/2013

DWG. NO.
ISPB350-SERIES

MATERIAL: 6061-T6511 ALUMINUM

SCALE: 1:2

SHEET: 1 OF 1