

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

15152 E Fremont Dr 80112-0000, CO Centennial Phone: 720-278-7555 Fax: 720-259-8851



ISR10C 1/0-14AWG 2PRT CLR SPLCR/RDCR Nsi Industries

Catalog Number	ISR10C
Manufacturer	Nsi Industries
Description	The Polaris Isr-1/0C Multi-Tap In-Line Entry Vision Tap Connector Features 2 Ports Sized For 1/0 - 14 Awg Wires. The Clear Body Allows Users to See Their Conductor Placement and Is Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Including Ins
Weight per unit	0.1500 (lbs/each)
Product Category	Small Terminals & Connectors
Features	
Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	1/0-14 AWG
Wire Type	Class B & C
Material, Color, and Finish	
Color	Clear
Finish	Plastisol Insulated
Housing Material	Aluminum
Dimensions and Weight	
Size	L=3.250 - W=.900 - H=1.480



ELLIOTT ELECTRIC SUPPLY 15152 E Fremont Dr 80112-0000, CO Centennial Phone: 720-278-7555 15152 E Fremont Dr 80112-0000, CO Centennial Phone: 720-278-7555

We Deliver...Lower Cost, Quality Products, & Personal Service

Fax: 720-259-8851

	2	~ r	1	•.	\sim	~~
	_					
_	es				v	
_			_		_	
			•			

Description	1/0-14AWG 2PRT CLR SPLCR/RDCR
extra long description	NSI ISR-1/0C POLARIS Vision Tap Spl
Features	The Polaris ISR-1/0C 2-Port In-Line Connector provides the simplest solution for forming a secure connection between two conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 1/0 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The clear body lets installers see their work for optimal conductor plac
Long Description	The Polaris ISR-1/0C Multi-Tap In-line Entry Vision Tap Connector features 2 ports sized for 1/0 - 14 AWG wires. The clear body allows users to see their conductor placement and is wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, including ins
Product Type	Polaris Vision Tap Splice 1/0
Special Features	1/0-14 AWG - Dual Rated

Manufacturer Information

Brand	Polaris
GTIN	00662381996459
Manufacturers Part Number	ISR-1/0C
UPC	662381996459

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Туре	IN-Line Splicer/Reducer

Packaging

Carton	4	
Weight Per each	0.15	

Uses, Certifications, and Standards

Application	Wire Termination
Enclosure	Clear Plastisol
environmental conditions	Dry Location Only
standard	UL 486A/B