



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ISRH750 750 MCM Splice *Nsi Industries*

| | |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | ISRH750 |
| Manufacturer | Nsi Industries |
| Description | The Polaris Isrh-750 Heavy-Duty Multi-Tap In-Line Entry Connector Features 2 Ports Sized For 750 MCM " 1/0 Awg Wires. The Body Is Made From Aluminum Alloy Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Double Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies, and Comes Packaged In A Clear Plastic Bag With A Mounting Hole For Hanging In Retail Disp |
| Weight per unit | 1.9 (lbs/each) |
| Product Category | Splicing & Terminating Kits |

Features

| | |
|----------------------|-------------|
| Material | Aluminum |
| Number of Conductors | 2 |
| Poles | 1 |
| Voltage Rating | 600 V |
| Warranty | 1 YEAR |
| Wire Size | 750-250 MCM |
| Wire Type | Class B & C |

Material, Color, and Finish

| | |
|--------|---------------------|
| Color | Black |
| Finish | Plastisol Insulated |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=7.250 - W=1.750 - H=3.250 |
|------|-----------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | 750 MCM SPLICE |
| extra long description | NSI ISRH-750 POLARIS Ins Splice HD |
| Features | The Polaris ISRH-750 2-Port In-Line Connector provides the simplest solution for forming a secure, heavy-duty connection between two conductors in splicing and reducing applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 750 MCM â€ 1/0 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The aluminum alloy body is wrap |
| Long Description | The Polaris ISRH-750 Heavy-Duty Multi-Tap In-Line Entry Connector features 2 ports sized for 750 MCM â€ 1/0 AWG wires. The body is made from aluminum alloy wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the double hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies, and comes packaged in a clear plastic bag with a mounting hole for hanging in retail disp |
| Product Type | Polaris Ins Splice HD 750 |
| Special Features | 750-250 MCM - Dual Rated |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Polaris |
| GTIN | 00662381926456 |
| Manufacturers Part Number | ISRH-750 |
| UPC | 662381926456 |

Taxonomies, Classifications, and Categories

| | |
|------|-------------------------|
| Type | IN-Line Splicer/Reducer |
|------|-------------------------|

Packaging

| | |
|-----------------|------|
| Carton | 2 |
| Weight Per each | 1.85 |

Uses, Certifications, and Standards

| | |
|--------------------------|------------------|
| Application | Wire Termination |
| environmental conditions | 90 C |
| standard | UL 486A/B |
| Temperature Rating | 90 C |