



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832



## IT010C 1/0-14AWG 2PRT, Os Insld Tap Conn

*Nsi Industries*

Catalog Number	IT010C
Manufacturer	Nsi Industries
Description	The Polaris Ito-1/0C Multi-Tap Offset Dual-Side Entry Vision Tap Connector Features 2 Ports Sized For 1/0 - 14 Awg Wires. The Clear Body Allows Users to See Their Conductor Placement and Is Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use In A Wide Range Of Splicing Applications, Incl
Weight per unit	0.1300 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

Number of Conductors	2
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR
Wire Size	1/0-14 AWG
Wire Type	Class B & C

### Material, Color, and Finish

Color	Clear
Finish	Plastisol Insulated
Housing Material	Aluminum

### Dimensions and Weight

Size	L=1.620 - W=1.750 - H=1.750
------	-----------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832

## Descriptions

Description	1/0-14AWG 2PRT,OS INSLTD TAP CONN
extra long description	NSI ITO-1/0C Polaris Vision Tap (CI
Features	The Polaris ITO-1/0C 2-Port Offset Dual-Sided Connector provides the simplest solution for forming a secure connection between two conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 1/0 - 14 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The clear body lets installers see their work for optimal cond
Long Description	The Polaris ITO-1/0C Multi-Tap Offset Dual-Side Entry Vision Tap Connector features 2 ports sized for 1/0 - 14 AWG wires. The clear body allows users to see their conductor placement and is wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use in a wide range of splicing applications, incl
Product Type	Polaris Vision Tap (Clear) 1/0-14 Awg Polaris Insulated Tap
Special Features	(2) 1/0-14 AWG - Dual Rated - Offset Ports

## Manufacturer Information

Brand	Polaris
GTIN	00662381996503
Manufacturers Part Number	ITO-1/0C
UPC	662381996503

## Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Offset Entry

## Packaging

Carton	6
Weight Per each	0.13

## Uses, Certifications, and Standards

Application	Wire Termination
Enclosure	Clear Plastisol
environmental conditions	Dry Location Only
standard	UL 486A/B