



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



IT350C 350MCM-9AWG 2PRT, 2SIDE CLR Insld Tap Conn

Nsi Industries

| | |
|------------------|---|
| Catalog Number | IT350C |
| Manufacturer | Nsi Industries |
| Description | The Polaris It-350C Multi-Tap Dual-Side Entry Vision Tap Connector Features 2 Ports Sized For 350 MCM to 6 Awg Wires. The Clear Body Allows Users to See Their Conductor Placement and Is Wrapped In A Layer Of Plastisol Insulation. Each Port Is Pre-Loaded With An Oxide Inhibitor, With Removable Access Plugs Over The Hex Screws Used to Tighten The Connections. Dual Rated For Use With Copper or Aluminum Cables. Installs With A Hex Key and Torque Wrench, Without Any Tape or Additional Supplies. Designed For Use |
| Weight per unit | 0.3900 (lbs/each) |
| Product Category | Large Terminals & Connectors |

Features

| | |
|----------------------|---------------|
| Material | Aluminum |
| Number of Conductors | 2 |
| Poles | 1 |
| Voltage Rating | 600 |
| Warranty | 1 YEAR |
| Wire Size | 350 MCM-6 AWG |
| Wire Type | Class B & C |

Material, Color, and Finish

| | |
|--------|---------------------|
| Color | Clear |
| Finish | Plastisol Insulated |

Dimensions and Weight

| | |
|------|-----------------------------|
| Size | L=2.470 - W=2.500 - H=2.440 |
|------|-----------------------------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 350MCM-9AWG 2PRT,2SIDE CLR INSLTD TAP CONN |
| extra long description | NSI IT-350C POLARIS Vision Tap 2 Po |
| Features | The Polaris IT-350C 2-Port Dual-Side Connector provides the simplest solution for forming a secure connection between two conductors in applications including cable trays, panel boards, ducts, raceways or troughs. Sized for 350 MCM to 6 AWG wires and rated for 600V, this pre-insulated connector comes pre-loaded with an oxide inhibitor and installs faster than traditional uninsulated connector options using just a hex key and torque wrench. The clear body lets installers see their work for optimal conductor |
| Long Description | The Polaris IT-350C Multi-Tap Dual-Side Entry Vision Tap Connector features 2 ports sized for 350 MCM to 6 AWG wires. The clear body allows users to see their conductor placement and is wrapped in a layer of plastisol insulation. Each port is pre-loaded with an oxide inhibitor, with removable access plugs over the hex screws used to tighten the connections. Dual rated for use with copper or aluminum cables. Installs with a hex key and torque wrench, without any tape or additional supplies. Designed for use |
| Product Type | Polaris Vision Tap 2 Port 350 |
| Special Features | (2) 350 MCM-6 AWG - Dual Rated |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Polaris |
| GTIN | 00662381996527 |
| Manufacturers Part Number | IT-350C |
| UPC | 662381996527 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type | Double Sided Entry |

Packaging

| | |
|-----------------|------|
| Carton | 4 |
| Weight Per each | 0.39 |

Uses, Certifications, and Standards

| | |
|--------------------------|-------------------|
| Application | Wire Termination |
| Enclosure | Clear Plastisol |
| environmental conditions | Dry Location Only |
| standard | UL 486A/B |
| Temperature Rating | 90 |