



# Undercabinet Lighting | Economy Halogen

Line Voltage 1-Lamp, 2-Lamp, 3-Lamp & 4-Lamp Fixtures



## Description

The Line Voltage Halogen luminaires are a modular system that provides economical halogen undercabinet lighting by utilizing 120-volt halogen lamps which do not require a transformer. Line voltage halogen lamps provide a warmer tone of light than low voltage halogen. These luminaires are optimized for fast, portable installation.

## Listing

UL/ C-UL Listed

## Finishes




Designer White

## Ordering Information\*

| Catalog No. | Description                  |
|-------------|------------------------------|
| UH106-WH    | 6", 1 Lamp, Designer White   |
| UH212-WH    | 12", 2 Lamps, Designer White |
| UH318-WH    | 18", 3 Lamps, Designer White |

\*Fixture includes: G8 120V 25W Bi-pin halogen lamp(s)  
6' Cord & Plug  
Joiner connector  
Mounting hardware




## Dimensions



## Features

- 120-volt, 25 watt halogen lamps provide a warmer tone than low voltage halogen lamps
- 2,000-hour lamp life
- Dimmable with standard incandescent wall box dimmers or integral high/low/off rocker switch
- Compact 3" D x 1-5/16" H extruded aluminum profile
- Internal specular reflector maximizes light output while managing fixture/cabinet contact temperature
- Modular design is optimized for portable plug-in installations and plug-together connection of multiple fixtures
- May be permanently direct wired using optional Direct Wire Module
- Available in Designer White finish

## Accessories

| Catalog No. | Description   |
|-------------|---|
| DWM1-WH     | Direct Wire Module, Designer White           |
| JC2-8-WH    | 8" Jumper Cord, Designer White  |
| JC2-17-WH   | 17" Jumper Cord, Designer White              |
| JC2-26-WH   | 26" Jumper Cord, Designer White   |
| T925        | G8 120V 25W Bi-pin Halogen Replacement Lamp  |