

Eaton JJS-50

Catalog Number: JJS-50

Eaton Bussmann series JJS fuse, Current-limiting, Small footprint, VFD line protection, 50 A, Class T, Non-indicating, Ferrule end x ferrule end, 200 kAIC at 600 V, Standard, 10, 600 V



General specifications

Product Name	Catalog Number
Eaton Bussmann series JJS fuse	JJS-50
UPC	Product Length/Depth
051712628501	1.56 in
Product Height	Product Width
0.81 in	0.81 in
Product Weight	Warranty
0.5 lb	Not Applicable
Compliances	
CE Marked	
RoHS Compliant	

Electrical rating

Amperage Rating

50 A

Interrupt rating

200 kAIC at 600 Vac

Voltage rating

600 V

Physical details

Packaging type

Standard

General information

Class

Class T

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Non-indicating

Resources

Catalogs

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - JJS-50

Technical data sheets

JJS-50~TRON FAST ACTING FUSE CLASS T

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)