



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



K11A30U Two:6 STR-300 Dual Rated

Burndy LLC

Catalog Number	K11A30U
Manufacturer	Burndy LLC
Description	Aluminum Universal Terminal, 1 Hole, Two: 6 Awg (STR)-300 Kcmil, 5/16" Stud, 2 Screws, Al/Cu Rated, Tin Plated.
Weight per unit	0.2300 (lbs/each)
Product Category	Large Terminals & Connectors

Features

Material	Aluminum
Number of Conductors	2

Descriptions

Description	TWO:6 STR-300 DUAL RATED
extra long description	BUR K11A30U TWO:6 STR-300 DUAL RATE
Long Description	Aluminum Universal Terminal, 1 Hole, Two: 6 AWG (Str)-300 kcmil, 5/16" Stud, 2 Screws, Al/Cu Rated, Tin Plated.
Product Type	Terminal
Special Features	Features: Dual-Rated Panelboard Lugs Are Constructed From High Strength Extruded Aluminum Alloy And Electro Tin-Plated To Provide Low Contact Resistance, Dimension T: 0.31 IN, Dimension N: 0.47 IN, Dimension D: 0.94 IN, Length: 3 IN, Installation Torque: 275 IN-LB, Width: 1 IN, Stud/bolt Hole Size: 5/16 IN, Height: 2 IN

Manufacturer Information

Brand	BURNDY
GTIN	00781810370261
Manufacturers Part Number	K11A30U
UPC	781810370261

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Bolted Lugs & Terminals

Packaging

Carton	1
Package	3
Weight Per each	0.23

Uses, Certifications, and Standards

Application	For Aluminum And Copper Conductors
standard	UL 486A-486B
Temperature Rating	194