

## Heavy Duty Channel

### FEATURES

- Steel housing with longitudinal ribs for extra strength
- Ballast cover retained by ¼ turn fasteners
- Individual or row mounting, surface, or suspended
- Channel ends double as joiners
- All metal parts are treated with a five stage phosphate bonding process and finished with a baked white enamel
- UL listed 1598, cUL or CSA. Damp Location standard



### ORDERING INFORMATION

<b>K</b>							
MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	LAMP TYPE		BALLAST	VOLTAGE	OPTIONS
<b>K</b> Heavy Duty Channel	4 4'	1 One	28	4', T5: 28 Watt	<b>NOTE:</b> See Technical Section for other ballast options. <b>E</b> Electronic T8, Instant Start <b>4E</b> 4-Lamp Electronic T8, Instant Start <b>EP</b> Electronic T5, T8, or T12 (96HO only), Programmed Start <b>4EP</b> 4-Lamp Electronic T5HO (N/A 347V) or T8, Programmed Start	<b>U</b> 120V-277V <b>347</b> 347V	<b>BC1</b> Branch Circuit Wiring, Single Circuit (For more branch circuit wiring options see page 113) <b>UN</b> Full Height End Channels <b>GLR</b> Fast Blow Fuse <b>EL</b> Emergency Battery Pack <b>PAF</b> Paint After Fabrication <b>NYC</b> NYC Compliant <b>NYCU</b> NYC Compliant, Union Label
	8 8'	2 Two	32	4', T8: 32, 30, 28 or 25 Watt			
	16 16' (Two housings)	See Product Availability table below.	48HO	4', T12: 60 Watt			
			54	4', T5HO: 54 or 51 Watt			
			96T8	8', T8: 59 Watt			
			96HO	8', T12: 110 or 95 Watt			
			96T8HO	8', T8: 86 Watt			

For more options see pages 96-112.


### ACCESSORIES (ORDER SEPARATELY)

- CSWG4** 4' Wire Guard (w/o reflector)
- CSR4** 4' Symmetric Reflector
- CSRA4** 4' Asymmetric Reflector
- S18** 18" Stem, 8° Swivel Stem and Canopy
- SS18** 18", 45° Swivel Stem and Canopy
- KHC** 24" Chain Hanger Assembly
- KTH** Tong Hanger (Pair)

For more accessories see pages 99-101.

### PRODUCT AVAILABILITY

SIZE	NO. OF LAMPS IN CROSS SECTION	NO. OF LAMPS IN FIXTURE	LAMP TYPE	WIDTH	LENGTH	HEIGHT
4'	1	1	28, 32, 48HO, 54	4 3/16"	48"	2 1/2"
	2	2	28, 32, 48HO, 54	4 3/16"	48"	2 1/2"
8'	1	1	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	96"	2 1/2"
	2	2	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	96"	2 1/2"
16' (Two housings)	1	2	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	192"	2 1/2"
	2	4	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	192"	2 1/2"



## Heavy Duty Channel

### FEATURES

- Steel housing with longitudinal ribs for extra strength
- Ballast cover retained by ¼ turn fasteners
- Individual or row mounting, surface, or suspended
- Channel ends double as joiners
- All metal parts are treated with a five stage phosphate bonding process and finished with a baked white enamel
- UL listed 1598, cUL or CSA. Damp Location standard



### ORDERING INFORMATION

MODEL	SIZE	NO. OF LAMPS IN CROSS SECTION	BALLAST	VOLTAGE	OPTIONS
<b>K</b> Heavy Duty Channel	4 4' 8 8' 16 16' (Two housings)	1 One 2 Two See Product Availability table below.	<b>NOTE:</b> See Technical Section for other ballast options. <b>E</b> Electronic T8, Instant Start <b>4E</b> 4-Lamp Electronic T8, Instant Start <b>EP</b> Electronic T5, T8, or T12 (96HO only), Programmed Start <b>4EP</b> 4-Lamp Electronic T5HO (N/A 347V) or T8, Programmed Start	<b>U</b> 120V-277V <b>347</b> 347V	<b>BC1</b> Branch Circuit Wiring, Single Circuit (For more branch circuit wiring options see page 113) <b>UN</b> Full Height End Channels <b>GLR</b> Fast Blow Fuse <b>EL</b> Emergency Battery Pack <b>PAF</b> Paint After Fabrication <b>NYC</b> NYC Compliant <b>NYCU</b> NYC Compliant, Union Label
<b>LAMP TYPE</b>					
28 4', T5: 28 Watt					
32 4', T8: 32, 30, 28 or 25 Watt					
48HO 4', T12: 60 Watt					
54 4', T5HO: 54 or 51 Watt					
96T8 8', T8: 59 Watt					
96HO 8', T12: 110 or 95 Watt					
96T8HO 8', T8: 86 Watt					

For more options see pages 96-112.

### ACCESSORIES (ORDER SEPARATELY)

- CSWG4** 4' Wire Guard (w/o reflector)
- CSR4** 4' Symmetric Reflector
- CSRA4** 4' Asymmetric Reflector
- S18** 18" Stem, 8° Swivel Stem and Canopy
- SS18** 18", 45° Swivel Stem and Canopy
- KHC** 24" Chain Hanger Assembly
- KTH** Tong Hanger (Pair)

For more accessories see pages 99-101.

### PRODUCT AVAILABILITY

SIZE	NO. OF LAMPS IN CROSS SECTION	NO. OF LAMPS IN FIXTURE	LAMP TYPE	WIDTH	LENGTH	HEIGHT
4'	1	1	28, 32, 48HO, 54	4 3/16"	48"	2 1/2"
	2	2	28, 32, 48HO, 54	4 3/16"	48"	2 1/2"
8'	1	1	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	96"	2 1/2"
	2	2	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	96"	2 1/2"
16' (Two housings)	1	2	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	192"	2 1/2"
	2	4	28, 54, 96T8, 96HO, 96T8HO	4 3/16"	192"	2 1/2"

