



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

KA4C  
 7818103614055  
 14-4 CU LUG ST SCR 1H  
 Active

**Web Use**  
 BURNDY Product Line

Dimensional	
Size (Hex) or Size (Bolt)	5/16
Length (in)	1.11
Thickness (in)	1/10
Height (in)	0.77
B Length (Fraction)	8/17
Hole Size (Fraction)	9/32
Stud Size (in)	1/4
Thickness	0.10
Size (Hex) or Size (Bolt) - in	0.31
B Length (in)	0.47
Pad Width (in)	0.54
N (Fraction)	1/4
N (in)	0.25
Hole Size (in)	0.28
Length (Fraction)	1-1/8
Height (Fraction) (in)	3/4
General	
Product Description	Copper Terminal, 1 Hole, 14 AWG (Sol)-4 AWG (Str), 1/4" Stud, 1 Screw
Conductor(s)	
Copper Solid Size (Range)	14 AWG-4 AWG
Copper Stranded (Range)	14 AWG-4 AWG
Physical	
Screw Type	Slot
Type of Hardware	5 / 16 "
Installation Torque	45
Type of Plating	Unplated
Connector Type	Terminal
Plated (Yes or No)	N
Product Material	Copper
Approvals / Certifications	
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

**BURNDY LLC - USA**

47 East Industrial Park Drive  
 Manchester NH 03109

**BURNDY Technical Services**

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175