



KAPO1/0, Wire range: #6 - 1/0 AWG, Torque: 100 N lb, Voltage: 600 V.

By Burndy
Catalog # [KAPO1/0](#)

Wire range: #6 - 1/0 AWG, Torque: 100 N lb, Voltage: 600 V.



General

Application	Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.
Catalog Number	KAPO1/0
Connector Type	Offset
EU RoHS Indicator	Contact Manufacturer
Hex Key	1/4 in
Installation Torque	100
Recommended in-lb	
Material	Aluminum
Sub Brand	Pin Adaptor
Type	#6 - 1/0 Mechanical Pin Adaptor; Off-Centered Pin
UPC	621945493353

Dimensions

Dimension - Strip Length inch	.97 in
Dimensions	2.01 in x 1.12 in x 1.43 in
Height	1.43 in
Length	2.01 in
Outside Diameter	1 in
Width	1.12 in

Electrical Ratings

Amperage Rating	170 A
-----------------	-------

Conductor Related

Conductor - AL Str Size Range	6 AWG - 1/0 AWG
Conductor - Copper DLO Size Range	6 AWG - 1/0 AWG
Conductor - Copper Flex H Size Range	6 AWG - 1/0 AWG
Conductor - Copper Flex I Size Range	6 AWG - 1/0 AWG
Conductor - Copper Flex K Size Range	6 AWG - 1/0 AWG
Conductor - Copper Str Size Range	6 AWG - 1/0 AWG
Conductor Size	6-1/0 AWG

Logistics

Carton Quantity	30
Minimum Pack Quantity	1
Pallet Quantity	2700

Product Assets

[Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
[Catalogs - BURNDY Master Catalog - Section A - Mechanical](#)
[Customer Notices - Prop 65 Notice](#)
[Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
[Sales Drawings - 50076514](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
BRDY-KAPO10-SPEC-EN | REV 6/2024